




# H-Series Dia-Vac - H302 (50 Hz)



**Max Pressure =** 60.0 PSIG (4.13 barG) **Parallel**  
60.0 PSIG (4.13 barG) **Series**  
**Max Vacuum =** 27.1 InHg (917 mBarG) **Parallel**  
29.5 InHg (999 mBarG) **Series**  
**Max Flow =** 69.1 SLPM (2.44 SCFM) **Parallel**  
36.0 SLPM (1.27 SCFM) **Series**

-Test results are averaged, and therefore should be considered approximate.  
-Tests performed with 316ss head, Teflon® diaphragm, 1/4 inch diameter hose x 5 ft. line at 75° F, using a std. 1725 RPM motor.  
-These test results are for reference only, and are intended to help provide information to the user when determining which pump to buy. Actual pump performance will depend upon the users' applications.  
-For 60 Hz operation, increase output by 20%.